

**Garant****Grinding point coarse, AR, Type: ZY4020****Order data**

Order number	550800 ZY4020
GTIN	4045197239426
Item class	51E

**Description****Version:**

**GARANT grinding points** (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Ceramic bonded grinding points in **pink aluminium oxide (AR)**. Medium-hard version. Coarse grit. Shank length 40 mm.

**Application:**

For general-purpose grinding of **unalloyed and low-alloy** steels and **cast iron**.

Recommended cutting speed 30 – 50 m/s.

**Technical description**

Shaft length	40 mm
Head Ø	40 mm
Grit designation	coarse
Shank Ø	6 mm
Head length	20 mm
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A

Product name attribute	AR
Type of product	Grinding point