

## Fine thread "Go" ring gauge 6g, M × pitch: 35X1,5



### Order data

|              |               |
|--------------|---------------|
| Order number | 486110 35X1,5 |
| GTIN         | 2050001041821 |
| Item class   | 48B           |

### Description

**Version:**

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

**Application:**

For metric ISO fine threads, right-hand DIN 13.

**Standard:**

Toleranzen und Abmaße nach **DIN ISO 1502**.

**Note:**

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

### Technical description

|                 |        |
|-----------------|--------|
| Thread pitch    | 1.5 mm |
| Tolerance class | 6g     |
| Thread          | M35    |
| Calibration     | L12    |

|                 |                        |
|-----------------|------------------------|
| Type of gauge   | "Go" plug gauge        |
| Tolerance zone  | g                      |
| Standard        | DIN 13                 |
| Thread type     | MF                     |
| Quality         | 6                      |
| Type of product | Thread "Go" ring gauge |

### Services

|   |            |
|---|------------|
| DAkkS calibration Thread "Go" ring gauge maximum $\varnothing$ 100 mm | 028640 100 |
| Calibration Thread ring gauge maximum $\varnothing$ 60 mm             | 028600 60  |