

## Fine thread "Go" plug gauge 6H, M × pitch: 55X1,5



### Order data

|              |               |
|--------------|---------------|
| Order number | 486120 55X1,5 |
| GTIN         | 2050001675750 |
| Item class   | 48B           |

### Description

#### Version:

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

**"Go" and "No Go" gauges are separate (DIN 2240, part 2, form GE).**

#### Application:

For metric ISO fine threads, right-hand DIN 13.

#### Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

#### Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

### Technical description

|                 |        |
|-----------------|--------|
| Thread pitch    | 1.5 mm |
| Thread          | M55    |
| Tolerance class | 6H     |
| Tolerance zone  | H      |
| Thread type     | MF     |
| Standard        | DIN 13 |
| Quality         | 6      |

|                 |                      |
|-----------------|----------------------|
| Type of gauge   | "Go" plug gauge      |
| Calibration     | L11                  |
| Type of product | Thread Go plug gauge |

### Services

|  |           |
|--|-----------|
| Calibration "Go" / "No Go" thread plug gauge maximum $\varnothing$ 60 mm       | 028500 60 |
| DAkkS calibration "Go" / "No Go" thread plug gauge maximum $\varnothing$ 90 mm | 028540 90 |