

Pipe threads "Go" / "No Go" plug gauge, Threads: G3/8in



Order data

Order number	486140 G3/8
GTIN	2050001035851
Item class	48B

Description

Version:

Plug thread gauges to DIN EN ISO 228-2. Ring thread gauges tolerance class A.
"No Go" gauges marked red.

Standard:

DIN EN ISO 228

Note:

Thread gauges for other diameters available on request.

Technical description

Thread	G3/8
Thread Ø	16.66 mm
Threads per inch	19
Tolerance class	A
Standard	DIN 228
Thread type	G
Tolerance zone	A
Type of gauge	"No Go" gauge
Type of gauge	"Go" plug gauge
Calibration	L10
Type of product	Thread Go / NoGo plug gauge

Services

DAkkS calibration "Go" / "No Go" thread plug gauge
maximum \varnothing 90 mm

028590 90

CalibrationGo / No Go thread plug gauge maximum \varnothing 20
mm

028550 20