

## Fine thread “No Go” plug gauge 6H, M × pitch: 50X1,5



### Order data

Order number	486130 50X1,5
GTIN	2050001675859
Item class	48B

### Description

#### Version:

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

**“Go” and “No Go” gauges are separate (DIN 2240, part 2, form GE).**

#### Application:

For metric ISO fine threads, right-hand DIN 13.

#### Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

#### Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

### Technical description

Thread	M50
Thread pitch	1.5 mm
Tolerance class	6H
Thread type	MF
Standard	DIN 13
Tolerance zone	H
Quality	6

Type of gauge	"No Go" gauge
Calibration	L11
Type of product	Thread NoGo plug gauge

**Services**

DAkkS calibration "Go" / "No Go" thread plug gauge maximum $\varnothing$ 90 mm	028540 90
Calibration "Go" / "No Go" thread plug gauge maximum $\varnothing$ 60 mm	028500 60