

## Fine thread "No Go" ring gauge 6g, M × pitch: 8X0,75



### Order data

|              |               |
|--------------|---------------|
| Order number | 486210 8X0,75 |
| GTIN         | 2050001036025 |
| Item class   | 48B           |

### Description

**Version:**

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

**Application:**

For metric ISO fine threads, right-hand DIN 13.

**Standard:**

Toleranzen und Abmaße nach **DIN ISO 1502**.

**Note:**

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

### Technical description

|                 |         |
|-----------------|---------|
| Tolerance class | 6g      |
| Thread pitch    | 0.75 mm |
| Thread          | M8      |
| Calibration     | L12     |

|                 |                           |
|-----------------|---------------------------|
| Tolerance zone  | g                         |
| Type of gauge   | "No Go" gauge             |
| Standard        | DIN 13                    |
| Thread type     | MF                        |
| Quality         | 6                         |
| Type of product | Thread "No Go" ring gauge |

### Services

|   |            |
|---|------------|
| DAkkS calibration Thread "Go" ring gauge maximum $\varnothing$ 100 mm | 028640 100 |
| Calibration Thread ring gauge maximum $\varnothing$ 20 mm             | 028600 20  |