

## Pipe threads "Go" / "No Go" plug gauge, Threads: G3/4in



### Order data

Order number	486140 G3/4
GTIN	2050001035875
Item class	48B

### Description

#### Version:

Plug thread gauges to DIN EN ISO 228-2. Ring thread gauges tolerance class A.  
"No Go" gauges marked red.

#### Standard:

**DIN EN ISO 228**

#### Note:

Thread gauges for other diameters available on request.

### Technical description

Threads per inch	14
Tolerance class	A
Thread Ø	26.44 mm
Thread	G3/4
Standard	DIN 228
Thread type	G
Tolerance zone	A
Type of gauge	"No Go" gauge
Type of gauge	"Go" plug gauge
Calibration	L10
Type of product	Thread Go / NoGo plug gauge

## Services

CalibrationGo / No Go thread plug gauge maximum  $\varnothing$  60 mm

028550 60

DAkkS calibration "Go" / "No Go" thread plug gauge maximum  $\varnothing$  90 mm

028590 90