

Fine thread “No Go” plug gauge 6H, M × pitch: 52X1,5



Order data

Order number	486130 52X1,5
GTIN	2050001675873
Item class	48B

Description

Version:

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

“Go” and “No Go” gauges are separate (DIN 2240, part 2, form GE).

Application:

For metric ISO fine threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

Technical description

Thread pitch	1.5 mm
Tolerance class	6H
Thread	M52
Standard	DIN 13
Thread type	MF
Quality	6
Tolerance zone	H

Type of gauge	"No Go" gauge
Calibration	L11
Type of product	Thread NoGo plug gauge

Services

Calibration "Go" / "No Go" thread plug gauge maximum \varnothing 60 mm	028500 60
DAkkS calibration "Go" / "No Go" thread plug gauge maximum \varnothing 90 mm	028540 90