

## Fine thread "Go" ring gauge 6g, M × pitch: 52X1,5



### Order data

Order number	486110 52X1,5
GTIN	2050001041739
Item class	48B

### Description

#### Version:

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

#### Application:

For metric ISO fine threads, right-hand DIN 13.

#### Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

#### Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

### Technical description

Thread pitch	1.5 mm
Tolerance class	6g
Thread	M52
Calibration	L12

Tolerance zone	g
Type of gauge	"Go" plug gauge
Standard	DIN 13
Thread type	MF
Quality	6
Type of product	Thread "Go" ring gauge

### Services

Calibration Thread ring gauge maximum $\varnothing$ 60 mm	028600 60
DAkkS calibration Thread "Go" ring gauge maximum $\varnothing$ 100 mm	028640 100