




## Grinding point hardness J fine, AW-CER, Type: ZY0205



### Order data

Order number	551791 ZY0205
GTIN	4007220898413
Item class	55E

### Description

#### Version:

**Fine**, 80 grit.

**PFERD grinding points** (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. PFERD grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Grinding point with **mixed grit (AW-CER)** in **hardness J**. Soft bonded combination of **white aluminium oxide** and **ceramic micro-crystalline sintered aluminium oxide** with high self-sharpening characteristics for consistently high metal removal rates coupled with cool grinding behaviour (Pferd designation AWCO).

#### Application:

For surface grinding of superalloys that are difficult to grind such as **titanium materials, nickel** and **cobalt-based alloys**, and also **hardened steel**.

Recommended cutting speed 30 – 50 m/s.

### Technical description

Grit	80
Grit designation	fine
Head Ø	2 mm
Shank Ø	3 mm
Head length	5 mm
Grinding media	Ceramic grit (CER)

Grinding medium code	Ceramic
Product name attribute	AW-CER
Type of product	Grinding point