

## Fine thread "Go" ring gauge 6g, M × pitch: 52X2



### Order data

Order number	486110 52X2
GTIN	2050001041746
Item class	48B

### Description

**Version:**

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

**Application:**

For metric ISO fine threads, right-hand DIN 13.

**Standard:**

Toleranzen und Abmaße nach **DIN ISO 1502**.

**Note:**

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

### Technical description

Thread	M52
Tolerance class	6g
Thread pitch	2 mm
Calibration	L12

Tolerance zone	g
Type of gauge	"Go" plug gauge
Standard	DIN 13
Thread type	MF
Quality	6
Type of product	Thread "Go" ring gauge

### Services

Calibration Thread ring gauge maximum $\varnothing$ 60 mm	028600 60
DAkkS calibration Thread "Go" ring gauge maximum $\varnothing$ 100 mm	028640 100