

**Flap wheel Fleece / cloth, fine, Head Ø×head width: 80X50mm****Order data**

Order number	554930 80X50
GTIN	4045197241160
Item class	52E

**Description****Version:**

Flap strips bonded on to the shank of the tool. Fleece is combined with abrasive cloth to **increases the abrasive effect** of the fleece. Shank Ø 6 mm.

**Application:**

For removal of dirt and oxide layers on metals as well as for matt finishing of Cr-Ni, other stainless steels, and also non-ferrous metals.

**Technical description**

Head width	50 mm
maximum speed	7000 min <sup>-1</sup>
recommended speed	4000 min <sup>-1</sup>
Shank Ø	6 mm
Head Ø	80 mm
Grinding medium code	A
Grit equivalent	280 / 240
Grit designation	fine

Product name attribute	fine
Type of product	Flap wheel

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		