

Pipe threads "No Go" plug gauge, Threads: G1.1/4in



Order data

Order number	486170 G1.1/4
GTIN	2050001035998
Item class	48B

Description

Version:

Plug thread gauges to DIN EN ISO 228-2. Ring thread gauges tolerance class A.
"No Go" gauges marked red.

Standard:

DIN EN ISO 228

Note:

Thread gauges for other diameters available on request.

Technical description

Thread	G1.1/2
Thread Ø	41.91 mm
Threads per inch	11
Tolerance class	A
Standard	DIN 228
Thread type	G
Tolerance zone	A
Type of gauge	"No Go" gauge
Calibration	L11
Type of product	Thread NoGo plug gauge

Services

Calibration "Go" / "No Go" thread plug gauge maximum \varnothing 60 mm	028500 60
DAkkS calibration "Go" / "No Go" thread plug gauge maximum \varnothing 90 mm	028540 90