

Fine thread "Go" plug gauge 6H, M × pitch: 50X2



Order data

Order number	486120 50X2
GTIN	2050001675729
Item class	48B

Description

Version:

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

"Go" and "No Go" gauges are separate (DIN 2240, part 2, form GE).

Application:

For metric ISO fine threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

Technical description

Tolerance class	6H
Thread	M50
Thread pitch	2 mm
Tolerance zone	H
Thread type	MF
Standard	DIN 13
Quality	6

Type of gauge	"Go" plug gauge
Calibration	L11
Type of product	Thread Go plug gauge

Services

DAkkS calibration "Go" / "No Go" thread plug gauge maximum \varnothing 90 mm	028540 90
Calibration "Go" / "No Go" thread plug gauge maximum \varnothing 60 mm	028500 60