

Pipe threads "No Go" plug gauge, Threads: G2in



Order data

| | |
|--------------|---------------|
| Order number | 486170 G2 |
| GTIN | 2050001045997 |
| Item class | 48B |

Description

Version:

Plug thread gauges to DIN EN ISO 228-2. Ring thread gauges tolerance class A.
"No Go" gauges marked red.

Standard:

DIN EN ISO 228

Note:

Thread gauges for other diameters available on request.

Technical description

| | |
|------------------|------------------------|
| Tolerance class | A |
| Thread | G2 |
| Thread Ø | 59.61 mm |
| Threads per inch | 11 |
| Standard | DIN 228 |
| Thread type | G |
| Tolerance zone | A |
| Type of gauge | "No Go" gauge |
| Calibration | L11 |
| Type of product | Thread NoGo plug gauge |

Services

DAkkS calibration "Go" / "No Go" thread plug gauge
maximum \varnothing 90 mm

028540 90

Calibration "Go" / "No Go" thread plug gauge maximum \varnothing
60 mm

028500 60