

HOLEX**Abrasive strip wheel (A), Ø 165 × 30 mm, Grit: 40****Order data**

Order number	555145 40
GTIN	4045197525659
Item class	52E

Description**Version:**

Abrasive strip wheels with **Aluminium Oxide (A)**. Bore Ø 54 mm.

Application:

Removing and cleaning up weld seams, grinding large areas, and workpieces that have an irregular profile.

Note:

For mounting on shafts smaller than Ø 54 mm, use the metal flange No. 555140, which can be bored out to suit. Other sizes available on request.

Technical description

Grit	40
Bore Ø	54 mm
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Disc Ø	165 mm

Disc thickness	30 mm
Product name attribute	Ø 165 × 30 mm
maximum speed	5200 min ⁻¹
Type of product	Abrasive strip wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable only under restricted conditions		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
dry	suitable		

Accessories

555140 54

Metal reducing flange pair, can be bored out suitable for
bore \varnothing 54 mm
