

Garant
Fleece abrasive star, Ø 19 mm, Grit equivalent: 280

Order data

Order number	555911 280
GTIN	
Item class	51E

Description
Version:

Star-shaped abrasive fleece with thread mounting. Tear-resistant and sturdy fleece body, no fraying at cut edges.

2-layer.

Application:

For cleaning, deburring, and finishing at hard-to-access places such as **bores, internal threads, pipes, and recesses**. Use clamping pin No. 555920.

Technical description

Grit designation	fine
Ø	19 mm
Colour	red
Grit equivalent	280
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 19 mm

recommended speed	10000 min ⁻¹
maximum speed	20000 min ⁻¹
Type of product	Flap disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		

Accessories

Clamping pin Overall length 75 mm	555920 75
-----------------------------------	-----------

Clamping pin Overall length 120 mm

555920 120