



Abrasive fleece ring set, 3 pieces (A), for cleaning and matting coarse, Ring Ø: 200mm



Order data

| | |
|--------------|---------------|
| Order number | 555760 200 |
| GTIN | 4013349627940 |
| Item class | 56Z |

Description

Version:

The **Unipol® fleece rings** are wound round a metal core; **each set contains three rings.**

Application:

The fleece rings can be clamped in any number and width.

Suitable for all metals (stainless steel, steel, aluminium, brass), plastics, wood, and ceramics.

Coarse and aggressive abrasive fleece (approx. 100 grit) for removal of rust film and superficial dirt. For roughening old paint, varnish, plastic, and rubber parts, for burnishing decorative metal surfaces (roughness Rt approx. 3.5 - 4 µm).

Note:

For clamping mandrels for fleece rings see No. 555785.

Technical description

| | |
|-----------------|--------|
| Bore Ø | 20 mm |
| Ring Ø | 200 mm |
| Reducing ring Ø | 14 mm |
| Reducing ring Ø | 16 mm |

| | |
|-----------------|----------------------|
| Ring width | 25 mm |
| Type of product | Abrasive fleece ring |

Accessories

| | |
|---|--------------|
| Polishing paste barUnipol® Colour WHITE | 555740 WHITE |
| Polishing paste barUnipol® Colour BLUE | 555740 BLUE |