

Garant**Fleece abrasive star, Ø 25 mm, Grit equivalent: 280****Order data**

Order number	555912 280
GTIN	4045197608970
Item class	51E

Description**Version:**

Star-shaped abrasive fleece with thread mounting. Tear-resistant and sturdy fleece body, no fraying at cut edges.

2-layer.

Application:

For cleaning, deburring, and finishing at hard-to-access places such as **bores, internal threads, pipes, and recesses**. Use clamping pin No. 555920.

Iron, sulphur and chlorine constituents: < 0.1 %

maximum speed: 20000 min⁻¹

Grit designation: fine

Colour: red

Technical description

Colour	red
Grit designation	fine
Ø	25 mm

Grit equivalent	280
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 25 mm
recommended speed	10000 min ⁻¹
maximum speed	20000 min ⁻¹
Type of product	Flap disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		

Accessories

Clamping pin Overall length 120 mm	555920 120
Clamping pin Overall length 75 mm	555920 75