

**Shim stock set 10 pieces 50×300 mm, Carbon steel, Thickness: 0,1mm****Order data**

Order number	478750 0,1
GTIN	2050001057440
Item class	48B

**Description****Version:**

Cold rolled, hard spring feeler strip steel of maximum precision. Shim thickness is marked and cannot be wiped off. Stored in sturdy boxes.

**C-steel** carbon steel, material No. 1.1274, cold rolled, hardened, bright surface (size 0.02 stainless).

**Application:**

**Setting** tools; **adjusting** devices; **balancing** tolerances; **shimming** components; **aligning** machines; **setting up** forms; **adjusting** bearing play; **adjusting** drive alignments; **setting** shear knives; **aligning** components etc.

**Supplied with:**

1 pack with 10 shim stocks.

**Technical description**

Thickness	0.1 mm
Material	Carbon steel
Error limit	±4 µm
Film width	50 mm
Film length	100 mm

Product name attribute	Carbon steel
Number of sheets	10
Type of product	Shim