



Angle polisher WPO, Type: 72214900



Order data

Order number	077712 72214900
GTIN	4014586862729
Item class	03F

Description

Version:

- **Stepless electronic speed control for optimum tool use.**
- **With spigot also applicable as a fully functional burnishing machine for longitudinal jobs.**
- **Very high speed stability at any load over the entire range.**
- **Automatic start inhibit against uncontrolled restart after power supply interruption.**

Supplied with:

Fein angle polisher WPO 14-25E, side handle.

Optional extras:

Standard surface finish set, No. 077718 size F, burnishing set for profiles, No. 077718 size S, polishing set, No. 077718 size P, pipework set, No. 077718 size R.

Technical description

Manufacturer's designation	WPO 14–25 E
maximum vibration to EN	3.5 m/s ²
Toolholder	M14
Speed range	900 - 2500 min ⁻¹
maximum polishing tool Ø	250 mm

Power consumption	1200 W
Weight	2.4 kg
Power supply	Mains operated
Type of product	Polishing machine

Accessories

Stainless steel set for WPO angle polisher Type S	077718 S
Stainless steel set for WPO angle polisher Type F	077718 F
Stainless steel set for WPO angle polisher Type R	077718 R