



## Power clamp adjustable long, Type: 4



### Order data

|              |               |
|--------------|---------------|
| Order number | 370091 4      |
| GTIN         | 4020772003159 |
| Item class   | 35A           |

### Description

#### Version:

- Clamping force 30 or 49 kN with tightening torque of approx. 100 Nm.
- Forged clamping element of alloy heat-treatable steel, black galvanised.
- Steplessly adjustable height and length.
- Low installed height.

#### Supplied with:

- Base element and carrier.
- T-nut DIN 508 with T-bolt strength class 12.9.

#### Optional extras:

Pressure pieces No. 370097.

### Technical description

|                     |             |
|---------------------|-------------|
| Clamping height h-H | 7 - 88 mm   |
| Clamping force      | 49 kN       |
| Adjustment travel V | 19 - 165 mm |
| L                   | 175 mm      |

|                                |               |
|--------------------------------|---------------|
| B                              | 75 mm         |
| Width across flats AF          | 12 mm         |
| B <sub>1</sub>                 | 25 mm         |
| A                              | 52 mm         |
| T-slot width                   | 22 mm         |
| Fastening screw G <sub>1</sub> | M24           |
| A <sub>1</sub>                 | 125 mm        |
| with height element            | no            |
| Fastening screw G              | M20           |
| Type                           | 764CC         |
| Type of product                | Sliding clamp |

## Accessories

|   |           |
|---|-----------|
| Spacer element long for type 4          | 370093 4  |
| Pressure piece, stainless steel Type DG | 370097 DG |
| Pressure piece, stainless steel Type DR | 370097 DR |