



Sliding clamps short, Type: 5



Order data

Order number	370092 5
GTIN	4020772003135
Item class	35A

Description

Version:

- Clamping force 30 or 49 kN with tightening torque of approx. 100 Nm.
- Forged clamping element of alloy heat-treatable steel, black galvanised.
- Steplessly adjustable height and length.
- Low installed height.

Supplied with:

- Base element and carrier.
- T-nut DIN 508 with T-bolt strength class 12.9.

Optional extras:

Pressure pieces No. 370095.

Technical description

Fastening screw G	M12
B ₁	18 mm
Clamping force	32 kN
A ₁	78 mm

Width across flats AF	8 mm
L	95 mm
T-slot width	14 mm
B	54 mm
A	36 mm
Clamping height h-H	6 - 50 mm
Fastening screw G ₁	M16
Adjustment travel V	12 - 82 mm
Type	764Md
Type of product	Sliding clamp

Accessories

Pressure pad, stainless steel Type DG	370095 DG
Pressure pad, stainless steel Type DR	370095 DR