

**HOLEX****Fleece velour-backed abrasive disc, Ø 115 mm, Grit equivalent: 280****Order data**

|              |               |
|--------------|---------------|
| Order number | 566940 280    |
| GTIN         | 4045197566195 |
| Item class   | 52E           |

**Description****Version:**

Fleece velour-backed abrasive discs with through-stitched backing for hook and loop fastener. With removable centre for more precise positioning and attachment of the disc to the backing pad (**approx. 50 % reduction in vibration level with velour-backed abrasive discs No. 566965**).

**Application:**

On angle grinders with hook and loop fastener backing pad No. 566960 or 566965. For **finishing, matting, smoothing** with significant reduction in roughness, and for **light cleaning** (such as removal of discolouration) and **deburring tasks**.

**Note:**

See No. **567705ff** onwards for velour-backed abrasive discs for rough abrasion.

**Technical description**

|                 |             |
|-----------------|-------------|
| Colour          | blue        |
| Grit equivalent | 280         |
| Version         | A very fine |

|   |                    |
|---|--------------------|
| Grit designation                        | fine               |
| Disc Ø                                  | 115 mm             |
| Grinding medium code                    | A                  |
| Iron, sulphur and chlorine constituents | < 0.1 %            |
| Product name attribute                  | Ø 115 mm           |
| maximum circumferential speed           | 40 m/s             |
| Type of product                         | Non-woven abrasive |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable                                  |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable                                  |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Paint                          | suitable                                  |                |          |
| Uni                            | suitable                                  |                |          |
| wet maximum                    | suitable only under restricted conditions |                |          |
| dry                            | suitable                                  |                |          |

## Accessories

Hook and loop backing pad with Centring and M 14 thread  
External Ø 115 mm

566965 115

Hook and loop backing pad with Thread M 14 External Ø  
115 mm

566960 115