



## Shim stock set 5 pieces 150×500 mm, stainless, Thickness: 0,15mm



### Order data

Order number	478760 0,15
GTIN	2050001057716
Item class	48B

### Description

#### Version:

Cold rolled, hard spring feeler strip steel of maximum precision. Shim thickness is marked and cannot be wiped off. Stored in sturdy boxes.

**Stainless** and acid resistant steel, material No. 1.4310 (or 1.4301 for thickness 0.02 and 0.05mm), cold rolled, spring hardened, bright surface.

#### Application:

**Setting** tools; **adjusting** devices; **balancing** tolerances; **shimming** components; **aligning** machines; **setting up** forms; **adjusting** bearing play; **adjusting** drive alignments; **setting** shear knives; **aligning** components etc.

#### Supplied with:

1 pack with 5 shim stocks.

### Technical description

Thickness	0.15 mm
Material	non-rusting and acid resistant stainless steel
Error limit	±5 µm
Film width	150 mm

Film length	500 mm
Product name attribute	stainless
Material	Stainless steel, INOX
Number of sheets	5
Type of product	Shim