



Shim stock 150×2500 mm, non-alloy steel, Thickness: 0,25mm



Order data

Order number	478700 0,25
GTIN	4045197207845
Item class	42H

Description

Version:

This precision gauging shim is provided on rolls in plastic boxes (easy to pull off). The individual boxes can be stacked in a block, saving space and protecting the material from dirt.

C-steel – Carbon steel, material No. 1.0330 (DC01 C490 MA), cold rolled, bright surface.

Application:

Setting tools; **adjusting** devices; **balancing** tolerances; **shimming** components; **aligning** machines; **setting up** forms; **adjusting** bearing play; **adjusting** drive alignments; **setting** shear knives; **aligning** components etc.

Technical description

Thickness	0.25 mm
Material	Carbon steel
Error limit	±7 µm
Film length	2500 mm
Film width	150 mm
Product name attribute	non-alloy steel
Type of product	Shim stock

