

**Shim stock set 5 pieces 150×500 mm, stainless, Thickness: 0,2mm****Order data**

Order number	478760 0,2
GTIN	2050001057723
Item class	48B

Description**Version:**

Cold rolled, hard spring feeler strip steel of maximum precision. Shim thickness is marked and cannot be wiped off. Stored in sturdy boxes.

Stainless and acid resistant steel, material No. 1.4310 (or 1.4301 for thickness 0.02 and 0.05mm), cold rolled, spring hardened, bright surface.

Application:

Setting tools; **adjusting** devices; **balancing** tolerances; **shimming** components; **aligning** machines; **setting up** forms; **adjusting** bearing play; **adjusting** drive alignments; **setting** shear knives; **aligning** components etc.

Supplied with:

1 pack with 5 shim stocks.

Technical description

Thickness	0.2 mm
Material	non-rusting and acid resistant stainless steel
Error limit	±6 µm
Film width	150 mm

Film length	500 mm
Product name attribute	stainless
Material	Stainless steel, INOX
Number of sheets	5
Type of product	Shim