

Pipe threads "No Go" ring gauge, Threads: G1/2in



Order data

| | |
|--------------|---------------|
| Order number | 486250 G1/2 |
| GTIN | 2050001036322 |
| Item class | 48B |

Description

Version:

Plug thread gauges to DIN EN ISO 228-2. Ring thread gauges tolerance class A.

"No Go" gauges marked red.

Standard:

DIN EN ISO 228

Note:

Thread gauges for other diameters available on request.

Technical description

| | |
|------------------|----------|
| Thread Ø | 20.96 mm |
| Threads per inch | 14 |
| Thread | G1/2 |
| Tolerance class | A |
| Calibration | L12 |
| Tolerance zone | A |

| | |
|-----------------|---------------------------|
| Type of gauge | "No Go" gauge |
| Thread type | G |
| Standard | DIN 228 |
| Type of product | Thread "No Go" ring gauge |

Services

| | |
|-----------------------------------------------------------------------|------------|
| Calibration Thread ring gauge maximum \varnothing 60 mm | 028600 60 |
| DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm | 028640 100 |