

## Pipe threads "No Go" ring gauge, Threads: G3/4in



### Order data

Order number	486250 G3/4
GTIN	2050001036339
Item class	48B

### Description

**Version:**

Plug thread gauges to DIN EN ISO 228-2. Ring thread gauges tolerance class A.

"No Go" gauges marked red.

**Standard:**

**DIN EN ISO 228**

**Note:**

Thread gauges for other diameters available on request.

### Technical description

Thread Ø	26.44 mm
Tolerance class	A
Thread	G3/4
Threads per inch	14
Calibration	L12
Tolerance zone	A

Type of gauge	"No Go" gauge
Standard	DIN 228
Thread type	G
Type of product	Thread "No Go" ring gauge

## Services

Calibration Thread ring gauge maximum $\varnothing$ 60 mm	028600 60
DAkkS calibration Thread "Go" ring gauge maximum $\varnothing$ 100 mm	028640 100