

3M Scotch-Brite™

Roll of abrasive fleece, 115 mm × 10 m, Fleece structure: 400**Order data**

Order number	556100 400
GTIN	4001895783968
Item class	53M

Description**Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding.

Advantage:

- **Adapts to the component shape.**
- **The open structure prevents clogging and reduces heat development.**
- **Even and reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

Application:

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Fine / very fine:** for cleaning delicate surfaces, for removing light scratches on metals. Also suitable for applying fine / very fine matt finishes to steels and non-ferrous metals.

Technical description

Fleece structure	400
Grit designation	fine
Grit equivalent	400 - 600

Colour	grey
Version	S Super Fine
3M designation	WR-SH
Iron, sulphur and chlorine constituents	< 0.1 %
Roller width	115 mm
Roll length	10 m
Product name attribute	115 mm × 10 m
Type of product	Roll of abrasive fleece

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		

dry

suitable

Accessories

Hand block

556020

Mandrel

556030