

3M Scotch-Brite™

Roll of abrasive fleece Durable Flex, 100 mm × 10 m, Fleece structure: 280**Order data**

Order number	556085 280
GTIN	4046719858262
Item class	53M

Description**Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding.

Flexible high-performance fleece with **extremely dense grit distribution** deep into the fibres of the material. The special type of fleece structure permits **more aggressive abrasive characteristics**, a very long working life without clogging and an even **more uniform finish**. The **enormous flexibility** enables use even in inaccessible places.

Advantage:

- **Adapts to the component shape.**
- **The open structure prevents clogging and reduces heat development.**
- **Even and reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

Application:

For manual cleaning and finishing, ideal substitute for steel wool products. **Medium / medium fine:** universally applicable to remove rust film, light soiling, discolouration; for rubbing down ground or brushed surfaces or for degreasing and cleaning prior to painting.

Technical description

Grit designation	medium fine
Grit equivalent	280 - 360
Colour	red
Fleece structure	280
Version	A Very Fine
3M designation	DF
Iron, sulphur and chlorine constituents	< 0.1 %
Roller width	100 mm
Roll length	10 m
Product name attribute	100 mm × 10 m
Type of product	Roll of abrasive fleece

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		

Uni	suitable
wet maximum	suitable only under restricted conditions
dry	suitable

Accessories

Mandrel	556030
Hand block	556020