

Pipe threads "No Go" ring gauge, Threads: G1in



Order data

Order number	486250 G1
GTIN	2050001036346
Item class	48B

Description

Version:

Plug thread gauges to DIN EN ISO 228-2. Ring thread gauges tolerance class A.
"No Go" gauges marked red.

Standard:

DIN EN ISO 228

Note:

Thread gauges for other diameters available on request.

Technical description

Threads per inch	11
Thread Ø	33.25 mm
Thread	G1
Tolerance class	A
Calibration	L12
Type of gauge	"No Go" gauge

Tolerance zone	A
Thread type	G
Standard	DIN 228
Type of product	Thread "No Go" ring gauge

Services

Calibration Thread ring gauge maximum \varnothing 60 mm	028600 60
DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	028640 100