

3M Scotch-Brite™

**Roll of abrasive fleece Durable Flex, 100 mm × 10 m, Fleece structure: 1000****Order data**

Order number	556085 1000
GTIN	4046719858309
Item class	53M

**Description****Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding.

**Flexible** high-performance fleece with **extremely dense grit distribution** deep into the fibres of the material. The special type of fleece structure permits **more aggressive abrasive characteristics**, a very long working life without clogging and an even **more uniform finish**. The **enormous flexibility** enables use even in inaccessible places.

**Advantage:**

- **Adapts to the component shape.**
- **The open structure prevents clogging and reduces heat development.**
- **Even and reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

**Application:**

For manual cleaning and finishing, ideal substitute for steel wool products. **Fine / ultra fine:** for cleaning delicate surfaces, for repairing light scratches on metals. Also suitable for applying fine / very fine matt finishes to steels and non-ferrous metals.

**Technical description**

Fleece structure	1000
Grit equivalent	600 - 1000
Grit designation	very fine
Colour	grey
Version	S Ultra Fine
3M designation	DF
Iron, sulphur and chlorine constituents	< 0.1 %
Roller width	100 mm
Roll length	10 m
Product name attribute	100 mm × 10 m
Type of product	Roll of abrasive fleece

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		

Uni	suitable
wet maximum	suitable only under restricted conditions
dry	suitable

---

## Accessories

Hand block	556020
Mandrel	556030