

**Shim stock set 5 pieces 150×500 mm, stainless, Thickness: 0,4mm****Order data**

Order number	478760 0,4
GTIN	2050001057754
Item class	48B

**Description****Version:**

Cold rolled, hard spring feeler strip steel of maximum precision. Shim thickness is marked and cannot be wiped off. Stored in sturdy boxes.

**Stainless** and acid resistant steel, material No. 1.4310 (or 1.4301 for thickness 0.02 and 0.05mm), cold rolled, spring hardened, bright surface.

**Application:**

**Setting** tools; **adjusting** devices; **balancing** tolerances; **shimming** components; **aligning** machines; **setting up** forms; **adjusting** bearing play; **adjusting** drive alignments; **setting** shear knives; **aligning** components etc.

**Supplied with:**

1 pack with 5 shim stocks.

**Technical description**

Thickness	0.4 mm
Material	non-rusting and acid resistant stainless steel
Error limit	±9 µm
Film width	150 mm

Film length	500 mm
Product name attribute	stainless
Material	Stainless steel, INOX
Number of sheets	5
Type of product	Shim