



## 3-point digital internal micrometer set, Measuring range: 40-100mm



### Order data

Order number	428841 40-100
GTIN	7630041117295
Item class	45A

### Description

#### Version:

Analogue 3-point internal micrometer for **high-precision measurement** of holes, even at large depths. Individual internal micrometer to Abbé's principle (no first order **tilt error**). Self-centring and self-aligning. Simple direct reading on the high-contrast display. Patented **CAPA  $\mu$ -measuring system**. Anvils titanium nitride (TIN) coated (HV5–2300).

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Digital internal micrometer No. 428830, extension No. 428802, with setting rings.

#### Optional extras:

Setting rings No. 484030, extensions No. 428802, data cable, radio remote control No. 498921, radio adapter No. 498924.

#### Note:

Centring devices for large measurement depths on request.

### Technical description

Number of setting rings	3
Setting ring $\varnothing$	50 / 70 / 90 mm

Measuring range	40 - 100 mm
Number of measuring heads	6
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 54
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	Digimatic interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

## Services

CalibrationInternal micrometer set Measuring range 40-100 mm	020550 40-100
---	---------------

## Accessories

Extension for IMICRO internal micrometer Type 4/500	428802 4/500
Setting ringDIN 2250 C Nominal size Ø 65 mm	484030 65
Setting ringDIN 2250 C Nominal size Ø 45 mm	484030 45
Setting ringDIN 2250 C Nominal size Ø 55 mm	484030 55
Setting ringDIN 2250 C Nominal size Ø 75 mm	484030 75
3-point digital internal micrometer IMICRO Measuring range 90-100 mm	428830 90-100

Extension for IMICRO internal micrometer Type 4/150	428802 4/150
Setting ringDIN 2250 C Nominal size Ø 85 mm	484030 85
3-point digital internal micrometer IMICRO Measuring range 40-50 mm	428830 40-50
Setting ringDIN 2250 C Nominal size Ø 95 mm	484030 95
Button cell / special battery Battery type CR2032	081560 CR2032