

**Garant****CC.T 09T302, Grade: HB7035-1**

## Order data

Order number	260056 HB7035-1
GTIN	4045197873705
Item class	21G

## Description

CCMT 09T302 HB7035-1 Grade: HB7035-1  
Chip breaker: SS  
Tolerance: M  
Cutting depth  $a_p$ : 0.2 - 2.5 mm  
Feed  $f$ : 0.05 - 0.25 mm/rev.  
Cutting speed  $v_c$  main application: 120 - 350 m/min

## Technical description

Corner radius	0.2 mm
Chip breaker	SS
Cutting depth $a_p$	0.2 - 2.5 mm
Grade	HB7035-1
Main application	P
Cutting conditions	heavily interrupted

Feed f	0.05 - 0.25 mm/rev.
Cutting speed $v_c$ main application	120 - 350 m/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 09T302
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning