

Garant**CC.T 09T302, Grade: HB7035-1**

Order data

Order number	260148 HB7035-1
GTIN	4045197873712
Item class	21G

Description

CC.T 09T302 HB7035-1 Grade: HB7035-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.2 - 4 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 100 - 320 m/min

Technical description

Main application	P
Chip breaker	SM
Cutting conditions	heavily interrupted
Feed f	0.1 - 0.3 mm/rev.
Corner radius	0.2 mm
Cutting depth a_p	0.2 - 4 mm
Grade	HB7035-1

Cutting speed v_c main application	100 - 320 m/min
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	CCMT 09T302
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning