


Garant**CCMT 120408, Grade: HB7035-1**

Order data

Order number	260066 HB7035-1
GTIN	4045197873781
Item class	21G

Description

CCMT 120408 HB7035-1 Grade: HB7035-1
Chip breaker: SS
Tolerance: M
Cutting depth a_p : 0.2 - 2.5 mm
Feed f : 0.05 - 0.25 mm/rev.
Cutting speed v_c main application: 120 - 350 m/min

Technical description

Corner radius	0.8 mm
Cutting speed v_c main application	120 - 350 m/min
Chip breaker	SS
Grade	HB7035-1
Main application	P
Cutting depth a_p	0.2 - 2.5 mm
Cutting conditions	heavily interrupted

Feed f	0.05 - 0.25 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 120408
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning