

3M Scotch-Brite™**Abrasive fleece hand pads, roll with 60 pieces Multiflex, 100×200 mm, Fleece structure: 1000****Order data**

Order number

556150 1000

GTIN

3134375314954

Item class

53M

Description**Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding. Hand-Pads of flexible and aggressive abrasive fleece.

Advantage:

- **Adapts to the shape of the component.**
- **The open structure prevents clogging and reduces heat development.**
- **Consistent reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

Application:

For manual cleaning and finishing, ideal substitute for steel wool products. **Fine / ultra fine:** for cleaning delicate surfaces, for repairing light scratches on metals. Also suitable for applying fine / very fine matt finishes to steels and non-ferrous metals.

Supplied with:

Roll with 60 pieces tear-off pads for dispensing.

Technical description

Fleece structure	1000
Grit equivalent	600 - 1000
Grit designation	very fine
Colour	grey
3M designation	MX
Version	S Ultra Fine
Iron, sulphur and chlorine constituents	< 0.1 %
Width	100 mm
Length	200 mm
Product name attribute	100×200 mm
Type of product	Abrasive fleece pad

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		

Uni	suitable
wet maximum	suitable only under restricted conditions
dry	suitable

Accessories

Mandrel	556030
Hand block	556020