

**Garant**
**CNMG 160612, Grade: HB7035-1**


### Order data

Order number	250336 HB7035-1
GTIN	4045197873965
Item class	21G

### Description

CNMG 160612 HB7035-1 Grade: HB7035-1  
 Chip breaker: SG  
 Cutting depth  $a_p$ : 1.5 - 8 mm  
 Feed  $f$ : 0.25 - 0.6 mm/rev.  
 Cutting speed  $v_c$  main application: 90 - 260 m/min

### Technical description

Cutting speed $v_c$ main application	90 - 260 m/min
Cutting conditions	heavily interrupted
Feed $f$	0.25 - 0.6 mm/rev.
Grade	HB7035-1
Cutting depth $a_p$	1.5 - 8 mm
Chip breaker	SG
Main application	P

Corner radius	1.2 mm
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	CNMG 160612
Number of changes/inserts	4
Type of product	Indexable insert for turning