

Garant
CNMG 160616, Grade: HB7035-1


Order data

Order number	250172 HB7035-1
GTIN	4045197873972
Item class	21G

Description

CNMG 160616 HB7035-1 Grade: HB7035-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 8 mm
 Feed f : 0.2 - 0.5 mm/rev.
 Cutting speed v_c main application: 100 - 320 m/min

Technical description

Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.5 - 8 mm
Corner radius	1.6 mm
Chip breaker	SM
Cutting speed v_c main application	100 - 320 m/min
Cutting conditions	heavily interrupted
Main application	P

Grade	HB7035-1
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	CNMG 160616
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning