

Garant
CNMM 120412, Grade: HB7035-1


Order data

Order number	250453 HB7035-1
GTIN	4045197874047
Item class	21G

Description

CNMM 120412 HB7035-1 Grade: HB7035-1
 Chip breaker: SR
 Cutting depth a_p : 2 - 10 mm
 Feed f : 0.4 - 1.2 mm/rev.
 Cutting speed v_c main application: 90 - 260 m/min

Technical description

Grade	HB7035-1
Chip breaker	SR
Cutting speed v_c main application	90 - 260 m/min
Cutting depth a_p	2 - 10 mm
Feed f	0.4 - 1.2 mm/rev.
Cutting conditions	heavily interrupted
Corner radius	1.2 mm

Main application	P
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	CNMM 120412
Number of changes/inserts	4
Type of product	Indexable insert for turning