

**Garant****DC.T 070202, Grade: HB7035-1**

## Order data

Order number	260351 HB7035-1
GTIN	4045197874092
Item class	21G

## Description

DCMT 070202 HB7035-1 Grade: HB7035-1  
Chip breaker: SS  
Tolerance: M  
Cutting depth  $a_p$ : 0.2 - 1.5 mm  
Feed  $f$ : 0.05 - 0.2 mm/rev.  
Cutting speed  $v_c$  main application: 120 - 350 m/min

## Technical description

Cutting speed $v_c$ main application	120 - 350 m/min
Cutting conditions	heavily interrupted
Corner radius	0.2 mm
Main application	P
Cutting depth $a_p$	0.2 - 1.5 mm
Feed $f$	0.05 - 0.2 mm/rev.

Grade	HB7035-1
Chip breaker	SS
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DCMT 070202
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning