

Garant
DC.T 11T304, Grade: HB7035-1


Order data

Order number	260359 HB7035-1
GTIN	4045197874153
Item class	21G

Description

DC.T 11T304 HB7035-1 Grade: HB7035-1
 Chip breaker: SS
 Tolerance: M
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.05 - 0.2 mm/rev.
 Cutting speed v_c main application: 120 - 350 m/min

Technical description

Chip breaker	SS
Cutting conditions	heavily interrupted
Corner radius	0.4 mm
Main application	P
Cutting depth a_p	0.2 - 1.5 mm
Grade	HB7035-1
Cutting speed v_c main application	120 - 350 m/min

Feed f	0.05 - 0.2 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DCMT 11T304
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning