

Garant**DC.T 11T308, Grade: HB7035-1**

Order data

Order number	260464 HB7035-1
GTIN	4045197874184
Item class	21G

Description

DC.T 11T308 HB7035-1 Grade: HB7035-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 2.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 100 - 320 m/min

Technical description

Main application	P
Feed f	0.1 - 0.3 mm/rev.
Grade	HB7035-1
Cutting conditions	heavily interrupted
Cutting speed v_c main application	100 - 320 m/min
Corner radius	0.8 mm
Chip breaker	SM

Cutting depth a_p	0.5 - 2.5 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	DCMT 11T308
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning