

Garant
DNMG 150612, Grade: HB7035-1


Order data

Order number	250764 HB7035-1
GTIN	4045197874283
Item class	21G

Description

DNMG 150612 HB7035-1 Grade: HB7035-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 5 mm
 Feed f : 0.2 - 0.5 mm/rev.
 Cutting speed v_c main application: 100 - 320 m/min

Technical description

Main application	P
Cutting speed v_c main application	100 - 320 m/min
Corner radius	1.2 mm
Cutting conditions	heavily interrupted
Grade	HB7035-1
Chip breaker	SM
Feed f	0.2 - 0.5 mm/rev.

Cutting depth a_p	0.5 - 5 mm
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	DNMG 150612
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning