

Garant
KNUX 160405L, Grade: HB7035-1

Order data

| | |
|--------------|-----------------|
| Order number | 251032 HB7035-1 |
| GTIN | 4045197874313 |
| Item class | 21G |

Description

KNUX 160405L HB7035-1 Grade: HB7035-1

Chip breaker: SM

Chip diverter: 2.2 mm

Cutting depth a_p : 0.5 - 5 mm

Feed f : 0.2 - 0.5 mm/rev.

Cutting speed v_c main application: 100 - 320 m/min

Technical description

| | |
|--------------------------------------|------------------------------------|
| Grade | HB7035-1 |
| Cutting speed v_c main application | 100 - 320 m/min |
| Cutting conditions | heavily interrupted |
| Corner radius | 0.5 mm |
| Cutting depth a_p | 0.5 - 5 mm |
| Feed f | 0.2 - 0.5 mm/rev. |
| Main application | P |
| Chip breaker | SM |
| Chip diverter | 2.2 mm |
| Finishing/roughing assignment | Skrubbearbejdning-sletbearbejdning |

| | |
|---------------------------|------------------------------|
| Tool material | Carbide |
| Number of changes/inserts | 2 |
| ISO code indexable insert | KNUX 160405L |
| Type of product | Indexable insert for turning |