

Garant
KNUX 160410L, Grade: HB7035-1

Order data

Order number	251078 HB7035-1
GTIN	4045197874375
Item class	21G

Description

KNUX 160410L HB7035-1 Grade: HB7035-1
 Chip breaker: SG
 Chip diverter: 3.2 mm
 Cutting depth a_p : 1 - 6 mm
 Feed f : 0.2 - 0.5 mm/rev.
 Cutting speed v_c main application: 90 - 260 m/min

Technical description

Grade	HB7035-1
Cutting speed v_c main application	90 - 260 m/min
Cutting depth a_p	1 - 6 mm
Chip breaker	SG
Corner radius	1 mm
Main application	P
Chip diverter	3.2 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting conditions	heavily interrupted
Finishing/roughing assignment	Roughing

Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160410L
Type of product	Indexable insert for turning