

**Garant**
**TCMT 110202, Grade: HB7035-1**


## Order data

Order number	260950 HB7035-1
GTIN	4045197874641
Item class	21G

## Description

TCMT 110202 HB7035-1 Grade: HB7035-1

Chip breaker: SS

Cutting depth  $a_p$ : 0.2 - 1.5 mm

Feed  $f$ : 0.05 - 0.2 mm/rev.

Cutting speed  $v_c$  main application: 120 - 350 m/min

## Technical description

Cutting depth $a_p$	0.2 - 1.5 mm
Corner radius	0.2 mm
Feed $f$	0.05 - 0.2 mm/rev.
Cutting conditions	heavily interrupted
Cutting speed $v_c$ main application	120 - 350 m/min
Chip breaker	SS
Grade	HB7035-1
Main application	P

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TCMT 110202
Number of changes/inserts	3
Type of product	Indexable insert for turning