

Garant
TC.T 110202, Grade: HB7035-1


Order data

Order number	260980 HB7035-1
GTIN	4045197874658
Item class	21G

Description

TC.T 110202 HB7035-1 Grade: HB7035-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 2.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 100 - 320 m/min

Technical description

Main application	P
Chip breaker	SM
Grade	HB7035-1
Cutting conditions	heavily interrupted
Cutting depth a_p	0.5 - 2.5 mm
Corner radius	0.2 mm
Cutting speed v_c main application	100 - 320 m/min
Feed f	0.1 - 0.3 mm/rev.

Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	TCMT 110202
Number of changes/inserts	3
Tolerance	M
Type of product	Indexable insert for turning